



Semi-Automatic Capping Machine CSAP-1 Model



Zona Industrial Pinhal Cascais, Lote 15 | 2560-112 Ponte do Rol – Torres Vedras
Phone: +351 261 312 132 | Email: geral@vismago.com | www.vismago.com

Semi-Automatic Capping Machine CSAP-1 Model

Applications:

Capsulation for all types of cylindrical bottles;

Characteristics:

- 316L stainless steel chassis;
- All components are made of 316L stainless steel;
- Pneumatic Motor with Torque;
- Torque Tuning;
- Tunable capping column for different bottle heights;
- Claws to hold the bottle, sharpenable to different flask diameters;

Technical characteristics:

Air supply: 4 bar to 6 bar



Zona Industrial Pinhal Cascais, Lote 15 | 2560-112 Ponte do Rol – Torres Vedras
Phone: +351 261 312 132 | Email: geral@vismago.com | www.vismago.com